

**metabo****Cordless sabre saw without battery, Type: SSEP18LTBL****Order data**

Order number	078223 SSEP18LTBL
GTIN	4061792250253
Item class	03D

**Description****Version:**

Powerful cordless sabre saw with low weight and angled softgrip handle for high working comfort.

- **Brushless motor for quick work progress and maximum efficiency.**
- **Depth stop adjustment without using tools.**
- **Vario (V) electronics for working at material-appropriate stroke rate.**
- **Saw blade can be rotated 180° for comfortable working above the head.**
- **Metabo Quick to change saw blades without the need for any tools.**
- **Selectable orbital stroke.**

**Advantage:**

**100% compatibility of the batteries – now also cross-manufacturer.**

All 18 V devices and battery packs from CAS partners are 100% compatible with each other. CAS stands for "Cordless Alliance System".

**Supplied with:**

Without battery and charger, in a cardboard box.

**Note:**

Sabre saw blades can be found from No. 588600.

See No. 073870 – No. 073890 for suitable batteries and chargers.

**Technical description**

Motor design	brushless
Weight	3 kg

maximum vibration to EN	14.5 m/s <sup>2</sup>
Power supply	Mains operated
Type of rechargeable battery	Lithium-ion
Rate of strokes	0 - 3000 min <sup>-1</sup>
Manufacturer's designation	SSEP 18 L BL
Stroke length	32 mm
suitable battery - supplier / battery type / voltage	Type CAS 18 V
Battery voltage	18 V
tool change without tools	yes
Type of product	Saw