



## Instant adhesive, 20 g, Type: BLACK



### Order data

Order number	083361 BLACK
GTIN	4067263117728
Item class	02A

### Description

#### Version:

Universally applicable for bonding dissimilar materials. Quick curing and clean, nearly invisible joints. Hardens by atmospheric humidity. Black instant adhesive, very well suited to connect materials with different coefficients of expansion. It is particularly suitable for **combined connections such as metal to rubber or metal to plastic**.

#### Note:

Not available in all countries. Express delivery not available.

### Technical description

Colour	black
Density	1.06 g/cm <sup>3</sup>
Tensile shear strength	18 - 28 N/mm <sup>2</sup>
Touch dry after	30 - 90 s
Shape	liquid
Dynamic viscosity	2000 - 4000 mPas

Operating temperature range	-55 - 95 °C
Storage temperature	20 °C
Labelling of hazardous substances	GHS07: Exclamation mark
Chemical basis	Ethyl cyanoacrylate
Capacity	20 ml
Product name attribute	20 g
Type of product	Instant adhesive