



Precision scales, type 572, maximum weighing range: 24000g



Order data

Order number	479521 24000
GTIN	4045761356931
Item class	47D

Description

Version:

- **Robust metal casing.**
- **Simple self-explanatory user guide.**
- **Selectable mains and battery operation.**
- **Units of weight (e.g. screw weight) can be freely programmed.**
- **Adjustment programme CAL: For accuracy adjustment (external calibration weight available on request if required).**
- **Quantity counting: Reference quantities selectable 1, 5, 10, 20 pieces. Display selectable between pieces and weight.**
- **Formulation: separate memory for weight of the tare vessel and of the formulation ingredients (net total).**
- **KERN Universal Port (KUP): allows the connection of external KUP interface adapters, such as RS-232 or USB, for exchanging data and control commands, without installation effort.**

Supplied with:

Mains adapter 230 V / 50 Hz and protective hood.

Optional extras:

External rechargeable battery, data cable, printer, interface adapter such as RS-232, USB on request.

Technical description

Dimensions of weighing plate	160×200 mm
Settling time	3 s
Minimum unit weight	1 g
Scale divisions	0.1 g
Reproducibility	0.1 g
Width	180 mm
Height	85 mm
Depth	310 mm
Power supply	Mains-powered
Power supply	Mains operated
maximum weighing range	0 - 24100 g
Linearity	±0.3 g
Manufacturer's designation	572
Net weight	2.7 kg
Calibration	Price on request
Type of product	Precision balance