



## Kraftform Kompakt RA VDE set, Number of pieces: 17



### Order data

Order number	667256 17
GTIN	4013288229694
Item class	63H

### Description

#### Version:

Kraftform handle with 154-mm-long **interchangeable blades fully insulated up to 1000 V to DIN EN IEC 60900 / VDE 06082-201**. The integral ratchet function (40 teeth/working arc 9°) simplifies and accelerates screwdriving without tedious repositioning. Reversing ring for left- and right-hand tightening and for fixed operation. Supplied in a sturdy textile folder with hook and loop fastening.

#### Advantage:

“Take it Easy” tool finder with colour marking by profiles – **to find the required tool quickly and easily.**

· **Sturdy maintenance-free gearbox of steel.**

#### Content:

Slot-head blades: 0.4×2.5; 0.6×3.5; 0.8×4.0; 1.0×5.5; 1.2×6.5

Blades for Phillips: PH1 and PH2

Pozidriv bits: PZ1 and PZ2

Pozidriv/slot-head blades (combination profile): PZ/ S1 and PZ/ S2 (combination profile)

blades for Torx®: Size TX10; TX15; TX20; TX25

Kraftform handle for interchangeable blades No. 667411: Gr.1

Kraftform handle with ratchet function: 1 piece

### Technical description

Drive profile	Slot-head screwdriver
Drive profile	Pozidriv screwdriver
Drive profile	Screwdriver for Phillips
Drive profile	Screwdriver for TORX® screws
Drive profile	Combination profile screwdriver Pozidriv/slot-head
Number of screwdrivers	17
Standard	DIN EN IEC 60900 / VDE 0682-201
Type of product	Screwdriver