


KOMET® Unisix® indexable insert, BK8425, Designation type W29: 34-130

Order data

Order number	237000 34-130
GTIN	4047109178182
Item class	24T

Description
Suitable for :

No. 236650; 236660; 236685; 236686

Note:

The standard application values refer to the KUB Trigon®.

Due to the special cutter geometry, the inserts can be used only for right-hand cutting KOMET KUB® indexable drill.

Type: INOX

ISO code indexable insert: WOEX 06T304

Feed f in steel $< 900 \text{ N/mm}^2$: 0.15 mm/rev.

Technical description

Designation	34-130
Feed f in steel $< 900 \text{ N/mm}^2$	0.15 mm/rev.
ISO code indexable insert	WOEX 06T304
Grade	BK8425
Type	INOX

Tool material	Carbide
Type of product	Indexable insert for drilling

User data

	Suitability	V _c	ISO code
Steel < 500 N/mm ²	suitable	300 m/min	P
Steel < 750 N/mm ²	suitable	250 m/min	P
Steel < 900 N/mm ²	suitable	200 m/min	P
INOX < 900 N/mm ²	suitable	160 m/min	M
INOX > 900 N/mm ²	suitable only under restricted conditions	160 m/min	M
Ti > 850 N/mm ²	suitable	80 m/min	S
wet maximum	suitable		