



## Welder's mask, automatic 3M™Speedglas™ G5-03 Pro VC, Colour: BLACK



### Order data

Order number	098005 BLACK
GTIN	4064035137441
Item class	040

### Description

#### Version:

The 3M™ Speedglas™ welder's mask G5-03 Pro was specially developed for the versatile welder. The mask has a **haptic touch function for switching between grinding and cutting mode**. Configurable with various accessories such as helmet lamp, neck protection and head protection. The ergonomic headband supports the high wearing comfort of the balanced helmet. Including welding filter G5-01/03VC (098006 G5-01/03). The 3M™ Speedglas™ **Variable Colour Technology** permits even better visual assessment and checking of the weld pool. The user can choose between a natural tone, cold tone or warm tone for the dark phase.

**Field of view of the welding filter:** 73 x 109 mm.

**Shade levels:** 8 – 14.

**Shade level in the light state:** 3. With lithium 3 V battery (working life 2,000 hours).

#### Application:

Particularly suitable for versatile welders who frequently have to grind and cut.

#### Standard:

EN ISO 16321; EN 379; EN 166

### Technical description

Classification to EN 379	1/1/1/2
--------------------------	---------

Type of rechargeable battery	Lithium-ion
Power supply	Mains operated
Manufacturer's designation	G5-03 Pro VC
Colour	black
Switching time from bright to dark	0.1 ms
Switching time from dark to bright	500 - 1300 ms
Number of rechargeable batteries contained	1
Field of view, welding filter [mm]	73 × 109 mm
Nominal voltage	3 V
Type of product	Welder's mask