



GÜNZBURGER STEIGTECHNIK

Platform ladder (push-fit), Type: 1



Order data

Order number	966286 1
GTIN	4031405520837
Item class	98G

Description

Version:

Single-sided access platform ladder with 2 aluminium handrails with trapezoidal platform. With 80 mm deep, corrugated steps (step spacing 235 mm), step/stile connection flanged on all 4 sides. 2 high-strength polyester belts prevent splay.

With practical shelf (350 × 200 mm) and "safe-cap" ladder joint. Flexibly expandable with optional plug-in parts, plug-in parts under No. 966288.

Standard:**EN 131**

Technical description

Material	Aluminium
Ladder length	1.43 m
Footprint width	0.57 m
Storage tray available	yes
Platform height without railing	0.69 m

Platform available	yes
wheeled	no
Working height approx.	2.7 m
Accessibility	single-sided
Cross beam height	73 mm
Number of steps including platform	3
Handrail	2
Length L	1.43 m
Rung/step depth	80 mm
Weight	9.5 kg
Ladders and platforms load capacity	150 kg
Type of product	Platform ladder