



GÜNZBURGER STEIGTECHNIK

FlexxTower mobile scaffolding, Platform height: 2100mm



Order data

Order number	966305 2100
GTIN	4031405951013
Item class	98G

Description

Version:

Mobile scaffolding made of stable aluminium round tube with welded frame parts. With aluminium toe boards and powder-coated guardrail frames with integrated knee bar for fall protection. Using a 3-T method, simple and safe assembly and disassembly from level to level by one person, use up to 2 persons. Tool-free installation thanks to plug connectors and quick-release fasteners. Low weight of the individual parts enables easy handling as well as space-saving transport and storage. Individual parts can be stacked compactly in one another and used as a tool trolley. With hinged triangular cantilevers with swivel base for high flexibility and stability – ideal also for wall-side construction or for moving in narrow aisles. Including 4 swivel castors \varnothing 125 mm, with parking brake, centric weight distribution and spindles. Height adjustment with level compensation.

Standard:

DIN EN 1004, Lastklasse/Gerüstgruppe 3, belastbar bis $2,0 \text{ kN/m}^2$.

Technical description

Working height approx.	4.1 m
Scaffolding height	3.3 m

Platform height	2100 mm
wheeled	yes
Number of wheels	4
Platform width	1200 mm
Platform depth	600 mm
Weight	80 kg
Transport dimension	1400×800×700 mm
Ladders and platforms load capacity	200 kg
Type of product	Scaffolding