



FlexxTower mobile scaffolding, Platform height: 4100mm



Order data

| | |
|--------------|---------------|
| Order number | 966305 4100 |
| GTIN | 4031405946637 |
| Item class | 98G |

Description

Version:

Mobile scaffolding made of stable aluminium round tube with welded frame parts. With aluminium toe boards and powder-coated guardrail frames with integrated knee bar for fall protection. Using a 3-T method, simple and safe assembly and disassembly from level to level by one person, use up to 2 persons. Tool-free installation thanks to plug connectors and quick-release fasteners. Low weight of the individual parts enables easy handling as well as space-saving transport and storage. Individual parts can be stacked compactly in one another and used as a tool trolley. With hinged triangular cantilevers with swivel base for high flexibility and stability – ideal also for wall-side construction or for moving in narrow aisles. Including 4 swivel castors \varnothing 125 mm, with parking brake, centric weight distribution and spindles. Height adjustment with level compensation.

Standard:

DIN EN 1004, Lastklasse/Gerüstgruppe 3, belastbar bis $2,0 \text{ kN/m}^2$.

Technical description

| | |
|----------------|---------|
| Weight | 117 kg |
| Platform width | 1200 mm |

| | |
|-------------------------------------|------------------|
| wheeled | yes |
| Working height approx. | 6.1 m |
| Platform height | 4100 mm |
| Number of wheels | 4 |
| Scaffolding height | 5.3 m |
| Platform depth | 600 mm |
| Transport dimension | 1400×800×1200 mm |
| Ladders and platforms load capacity | 200 kg |
| Type of product | Scaffolding |