



## FlexxTower mobile scaffolding, Platform height: 3100mm



### Order data

Order number	966305 3100
GTIN	4031405951020
Item class	98G

### Description

#### Version:

Mobile scaffolding made of stable aluminium round tube with welded frame parts. With aluminium toe boards and powder-coated guardrail frames with integrated knee bar for fall protection. Using a 3-T method, simple and safe assembly and disassembly from level to level by one person, use up to 2 persons. Tool-free installation thanks to plug connectors and quick-release fasteners. Low weight of the individual parts enables easy handling as well as space-saving transport and storage. Individual parts can be stacked compactly in one another and used as a tool trolley. With hinged triangular cantilevers with swivel base for high flexibility and stability – ideal also for wall-side construction or for moving in narrow aisles. Including 4 swivel castors  $\varnothing$  125 mm, with parking brake, centric weight distribution and spindles. Height adjustment with level compensation.

#### Standard:

DIN EN 1004, Lastklasse/Gerüstgruppe 3, belastbar bis  $2,0 \text{ kN/m}^2$ .

### Technical description

wheeled	yes
Number of wheels	4

Weight	102 kg
Platform depth	600 mm
Platform width	1200 mm
Platform height	3100 mm
Scaffolding height	4.3 m
Working height approx.	5.1 m
Transport dimension	1400×800×900 mm
Ladders and platforms load capacity	200 kg
Type of product	Scaffolding