



## Nibblers, Type: 7232466



### Order data

Order number	078111 7232466
GTIN	4014586897677
Item class	03F

### Description

#### Version:

- **Very economical operating costs due to long working life of die and matrix.**
- **QuickIN quick-change system for quick die and matrix changing without tools**
- **Working direction can be changed without tools.**

Powerful nibbler with unlimited curve manoeuvrability for recesses and cut-outs.

#### Note:

Suitable batteries can be found under No. 073851 – No. 073858 or starter set under No. 073863 – No. 073867. Chargers are listed under No. 073866.

### Technical description

maximum vibration to EN	< 2,5 m/s <sup>2</sup>
Packaging	Modular case (L-Boxx)
Radius of the smallest curve	7 mm
Cutting speed	1.5 m/min
maximum material thickness steel 800 N/mm <sup>2</sup>	1.8 mm
Power consumption	1700 W
Weight	3.6 kg

Mains frequency	50 Hz
Cutting width	14 mm
Rate of strokes	820 min <sup>-1</sup>
AC supply voltage	230 V
Power supply	Mains-powered
maximum material thickness steel 400&nbsp;N/mm <sup>2</sup>	3.5 mm
Manufacturer's designation	BLK 3.5E
Type of product	Nibblers