



Nibblers, Type: 7232476



Order data

Order number	078111 7232476
GTIN	4014586897714
Item class	03F

Description

Version:

- **Very economical operating costs due to long working life of die and matrix.**
- **QuickIN quick-change system for quick die and matrix changing without tools**
- **Working direction can be changed without tools.**

Powerful nibbler for heavy-duty dismantling and cutting work.

Note:

Suitable batteries can be found under No. 073851 – No. 073858 or starter set under No. 073863 – No. 073867. Chargers are listed under No. 073866.

Technical description

Packaging	Modular case (L-Boxx)
Weight	3.8 kg
Power consumption	1700 W
Rate of strokes	820 min ⁻¹
Manufacturer's designation	BLK 5.0
maximum material thickness steel 400 N/mm ²	5 mm
Radius of the smallest curve	90 mm

AC supply voltage	230 V
Mains frequency	50 Hz
maximum vibration to EN	< 2,5 m/s ²
Cutting speed	1.3 m/min
Power supply	Mains-powered
maximum material thickness steel 800 N/mm ²	2.5 mm
Cutting width	8 mm
Type of product	Nibblers