

**Battery / mains radio, Type: 4933492344****Order data**

Order number	073960 4933492344
GTIN	4058546417116
Item class	03L

Description**Version:**

Sturdy site radio, splash-proof (IP54) for mains and battery operation. Bluetooth cordless radio with powerful audio system.

- **Shock-absorbing end caps to protect against falls**
- **USB-C port for charging mobile devices**
- **Up to 13 hours of operation with a Milwaukee 18 V/5 Ah rechargeable battery.**
- **Operation with Milwaukee 18 V batteries or with 230 V mains voltage.**

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

Includes mains cable, 2 back-up batteries, AUX connection cable, without batteries.

Technical description

Weight	5 kg
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
Height	218 mm

IP Index of Protection	IP 54
Power supply	Mains operated
Power supply	Mains-powered
Interface	Bluetooth interface
Interface	USB interface
Battery voltage	18 V
Width	228 mm
Type of rechargeable battery	Lithium-ion
Manufacturer's designation	M18RADDAB+G2-018V/-
Length	515 mm
Number of rechargeable batteries contained	0
Type of product	Radio