

metabo**Cordless jigsaw without rechargeable battery, Type: ST18L90****Order data**

Order number	078185 ST18L90
GTIN	4061792256170
Item class	03D

Description**Version:**

Robust and extremely easy to use cordless jigsaw for **precise cuts**.

- **Variable stroke rate, pendulum stroke and low-lying, spring-assisted saw blade guidance.**
- **Switchable chip blowing function ensures a clear view of the interface.**
- **Small handle circumference and softgrip surface.**

The everyday helper for your sawing tasks: handy cordless jigsaw for cuts in wood of up to 90 mm.

- **Chip blowing function for a clear view of the interface.**
- **Extraction capability, restart protection.**

Advantage:

Batteries are 100% compatible – now also across different manufacturers.

All 18 V devices and battery packs from CAS partners are 100% compatible with each other. CAS stands for "Cordless Alliance System".

Supplied with:

Without battery and charger, including suction nozzle, protective glass and hexagon key.
Supplied with chip break guard.

Note:

See No. 073870 – 073890 for suitable batteries and chargers.

Technical description

maximum vibration to EN	8.7 m/s ²
Special features	Small handle circumference
Rate of strokes	750 - 3000 min ⁻¹
Manufacturer ID	ST 18 L 90
suitable battery - supplier / battery type / voltage	Type CAS 18 V
Orbital stroke	4-fold
Battery voltage	18 V
tool change without tools	Yes, Metabo Quick
Format	Straight handle
maximum sawn thickness steel	10 mm
Manufacturer's designation	ASTS 18-26 AS
Power supply	Mains operated
Mitre angle adjustment	yes
Weight	1.9 kg
maximum sawn thickness wood	90 mm
Number of rechargeable batteries contained	0
Type of rechargeable battery	Lithium-ion
Type of product	Saw