

metabo
Cordless drill / driver without rechargeable battery with Quick System, Type: 613156850


Order data

Order number	070271 613156850
GTIN	4061792246232
Item class	03D

Description

Version:

Cordless drill drivers with and without Metabo Quick System.

The **Quick System saves a lot of time** when switching frequently between drilling and screwdriving. The drill chuck with drill is exchanged for bit holders and bits within a matter of seconds, without any tools.

Choose between a **complete set** of 2 battery packs, charger and a robust plastic case or the **machine without accessories** in a box if you already have some batteries. Of course, you can also purchase battery packs and chargers separately. By the way, all Metabo battery packs are covered by a **3-year warranty**, regardless of the number of charging cycles.

Additional details such as the bright **LED work light** and the practical **belt hook** provide even more comfort when working.

- **Precision Stop: more precise electronic torque coupling for exact, sensitive working.**
- **Selectable pulse mode for unscrewing jammed screws and spot drilling on smooth surfaces.**

Advantage:

Batteries are 100% compatible – now also across different manufacturers.

All 18 V devices and battery packs from CAS partners are 100% compatible with each other. CAS stands for "Cordless Alliance System".

Supplied with:

With quick-change drill chuck, without battery, without charger.

Note:

See No. 073870 – 073890 for suitable batteries and chargers.

Technical description

Quick-clamping chuck range	1.5 - 13 mm
Power supply	Mains operated
maximum twist drill size Ø in wood	40 mm
Type of rechargeable battery	Lithium-ion
Battery voltage	18 V
suitable battery - supplier / battery type / voltage	Type CAS 18 V
Packaging	Metabox
No load speed	0 - 500 min ⁻¹
No load speed	0 - 1700 min ⁻¹
Manufacturer's designation	BS 18 L BL Q
typical application	Medium
Number of rechargeable batteries contained	0
Motor design	brushless
maximum torque hard	65 Nm
Weight without battery	0.9 kg
maximum twist drill size Ø in steel	13 mm
maximum torque soft	28 Nm
Type of product	Drill/drivers
USP1	18V
USP2	Brushless motor, quick-change chuck clamping range 1.5-13, without battery

Accessories

Battery packLi-Power Battery capacity 2 A·h	073870 2
Battery packLi-Power Battery capacity 4 A·h	073870 4
Battery packLi-Power Battery capacity 5,2 A·h	073870 5,2
Battery charger Type ASC145	073890 ASC145
Battery charger Type ASC55	073890 ASC55
Battery charger Type ASC55-8	073890 ASC55-8