

**metabo****Cordless drill/driver with Li-ion rechargeable battery, Type: 613155500****Order data**

Order number	070260 613155500
GTIN	4061792245839
Item class	03D

**Description****Version:****Cordless drill/driver with and without Metabo Quick system.**

The **Quick system saves a lot of time** if you frequently need to change between drilling and screwing. In just a few seconds, the drill chuck with drill can be replaced with a bit holder and a bit, without the need for any tools.

Choose between a **complete set** with 2 battery packs, charger and sturdy plastic case, or the **machine without accessories** in the box if you already have a few batteries. Of course, you can also buy battery packs and chargers separately. All battery packs from Metabo come with a **3-year warranty**, irrespective of the number of charge cycles.

Further highlights such as the bright **LED work light** and the handy **belt hook** ensure even greater convenience when working.

**Advantage:****Batteries are 100% compatible – now also across different manufacturers.**

All 18 V devices and battery packs from CAS partners are 100% compatible with each other. CAS stands for "Cordless Alliance System".

**Supplied with:**

Supplied with quick-change chuck, 2 pcs. rechargeable battery, charger and metaBOX.

**Note:**

See No. 073870 – 073890 for suitable batteries and chargers.

## Technical description

maximum twist drill size Ø in wood	40 mm
Power supply	Mains operated
Weight without battery	0.9 kg
Battery capacity	2 Ah
Motor design	brushless
Packaging	Metabox
Manufacturer's designation	BS 18 L BL
suitable battery - supplier / battery type / voltage	Type CAS 18 V
maximum torque soft	28 Nm
Type of rechargeable battery	Lithium-ion
Battery voltage	18 V
No load speed	0 - 500 min <sup>-1</sup>
No load speed	0 - 1700 min <sup>-1</sup>
maximum torque hard	65 Nm
maximum twist drill size Ø in steel	13 mm
Number of rechargeable batteries contained	2
Quick-clamping chuck range	1.5 - 13 mm
typical application	Medium
Type of product	Drill/drivers
USP1	18V
USP2	Quick-change chuck clamping range 1.5-13, in METABOX

## Accessories

Battery packLi-Power Battery capacity 2 A·h	073870 2
Battery charger Type ASC145	073890 ASC145
Battery charger Type ASC55	073890 ASC55

Battery charger Type ASC55-8

073890 ASC55-8