

metabo**Cordless hammer drill with Li-ion battery, Type: 613157500****Order data**

Order number	070121 613157500
GTIN	4061792245945
Item class	03D

Description**Version:****Cordless hammer drill with brushless motor and two-speed gearbox.**

Choose between a complete set of 2 battery packs, charger and sturdy plastic case or the machine without accessories in a box if you already have a few batteries. Of course, you can also buy battery packs and chargers separately.

By the way, all Metabo battery packs come with a 3-year warranty, irrespective of the number of charging cycles.

Further details such as the bright LED work light and the handy belt hook ensure even more comfort when working.

- **Cordless impact drill/driver with extremely compact design for universal applications.**
- **Impact drilling function for drilling in masonry.**

Advantage:**Batteries are 100% compatible – now also across different manufacturers.**

All 18 V devices and battery packs from CAS partners are 100% compatible with each other. CAS stands for "Cordless Alliance System".

Supplied with:

Supplied with quick-change chuck, 2 pcs. Li-ion rechargeable battery, charger and metaBox.

Note:

See No. 073870 – 073890 for suitable batteries and chargers.

Technical description

Number of rechargeable batteries contained	2
Weight without battery	0.9 kg
Type of rechargeable battery	Lithium-ion
Quick-clamping chuck range	1.5 - 13 mm
maximum twist drill size Ø in steel	13 mm
Motor design	brushless
maximum hammer rate	25500 min ⁻¹
Battery capacity	2 Ah
Manufacturer's designation	SB 18 L BL
maximum torque hard	65 Nm
maximum torque soft	28 Nm
suitable battery - supplier / battery type / voltage	Type CAS 18 V
No load speed	0 - 1700
No load speed	0 - 500
typical application	Medium
Power supply	Mains operated
maximum twist drill size Ø in wood	40 mm
maximum twist drill size Ø in concrete	13 mm
Battery voltage	18 V
Packaging	Metabox
Type of product	Impact drill /screwdriver