

 steinel**Heat gun, Type: 89504****Order data**

Order number	078321 89504
GTIN	4007841089504
Item class	07E

**Description****Version:**

**High-quality straight handle heat gun HM 2620 E** for professional applications. Electronically controlled with stepless regulation of the air quantity.

**Application:**

For welding and forming plastics, for shrinking, removing paints, soldering, drying, and thawing.

**Technical description**

AC supply voltage	230 V
Mains frequency	50 Hz
Air flow volume	150 - 500 l/min
Air temperature	50 - 700 °C
Weight	840 g
Power supply	Mains-powered
Power consumption	2300 W
Manufacturer's designation	HM 2620 E
Type of product	Hot air pistol