

Garant
GARANT Power Drill indexable drill Combination shank, 3xD, Ø DC m7: 15,5mm

Order data

Order number	234005 15,5
GTIN	4045197696410
Item class	21S

Description
Version:

The helical coolant ducts ensure very high stability, since they do not weaken the core of the drill.

Bore tolerance: $-0.1 / +0.3$ mm

Description:

For maximum performance and dimensional accuracy. Even for very difficult drilling situations up to $5 \times D$.

Application:

With indexable inserts No. 234030 - 234098.

Use of the advertising text:

With inserts No. GG2340 - GG2389.

Suitable for:

Inserts SOGX 050204.

Note:

Other intermediate sizes in 1/10 increments available on request.

Technical description

ISO code indexable insert	SOGX 050204
Shank $\varnothing D_s$	20 mm
Pack of insert screws	239700 5IP (0.38 Nm)
Number of cutting edges Z	1
Reach L_1	48 mm

Shank length L_s	50 mm
Series	Power Drill
Nominal $\varnothing D$	15.5
Maximum adjustment limit V_{max}	0.25 mm
Overhang L_A	64 mm
Indexable insert type for internal cutter	HB6535
Indexable insert type for internal cutter	HB6640
Indexable insert type for internal cutter	HB630
Indexable insert type for internal cutter	HB6810
Drill depth for indexable insert drill up to	3×D
Shank	ISO 9766
Use for drilling	limited centre drilling
Use for drilling	limited convexity
Use for drilling	limited cross-drilling
Use for drilling	limited drilling through a stack
Use for drilling	limited drilling with oblique exit
Use for drilling	limited cross-drilling
Through-coolant	yes
Machining strategy	HPC
Type of product	Indexable drill

Accessories

PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 5IP	674252 5IP
Torque screwdriver, fixed setting set torque 0,38 N·m	211750 0,38
Torx Plus® insert screw set 10 pieces Drive 5IP	239700 5IP