



## Cordless hammer drill without battery, Type: 602360650

### Order data

|              |                  |
|--------------|------------------|
| Order number | 070122 602360650 |
| GTIN         | 4061792188174    |
| Item class   | 03D              |

### Description

#### Version:

#### **Cordless hammer drill / driver with brushless motor and two-speed gearbox.**

Choose between a complete set with 2 battery packs, charger and sturdy plastic case, or the machine without accessories in the box if you already have a few batteries. Of course, you can also buy battery packs and chargers separately.

All battery packs from Metabo come with a 3-year warranty, irrespective of the number of charge cycles.

Further highlights such as the bright LED work light and the handy belt hook ensure even greater convenience when working.

#### **Advantage:**

#### **Batteries are 100% compatible – now also across different manufacturers.**

All 18 V devices and battery packs from CAS partners are 100% compatible with each other. CAS stands for "Cordless Alliance System".

#### **Supplied with:**

Supplied with quick-change chuck; without rechargeable battery, charger and transport case.

#### **Note:**

See No. 073870 – 073890 for suitable batteries and chargers.

### Technical description

|  |               |
|--|---------------|
| suitable battery - supplier / battery type / voltage | Type CAS 18 V |
| Number of rechargeable batteries contained           | 0             |
| Motor design   | brushless     |
| Packaging  | Metabox       |
| maximum twist drill size Ø in concrete               | 16 mm         |
| No load speed  | 0 - 550       |

## Data sheet

|                                     |                           |
|-------------------------------------|---------------------------|
| No load speed                       | 0 - 2000                  |
| Type of rechargeable battery        | Lithium-ion               |
| maximum twist drill size Ø in steel | 13 mm                     |
| Manufacturer's designation          | SB 18 LTX BL I            |
| typical application                 | Heavy Duty                |
| maximum hammer rate                 | 38000 min <sup>-1</sup>   |
| Battery voltage                     | 18 V                      |
| Quick-clamping chuck range          | 1.5 mm                    |
| Weight without battery              | 2.5 kg                    |
| maximum twist drill size Ø in wood  | 68 mm                     |
| maximum torque hard                 | 130 Nm                    |
| maximum torque soft                 | 65 Nm                     |
| Type of product                     | Impact drill /screwdriver |