

**metabo****Cordless drill / driver without rechargeable battery, Type: 602358650****Order data**

|              |                  |
|--------------|------------------|
| Order number | 070261 602358650 |
| GTIN         | 4061792188136    |
| Item class   | 03D              |

**Description****Version:****Cordless drill drivers with and without Metabo Quick System.**

The **Quick System saves a lot of time** when switching frequently between drilling and screwdriving. The drill chuck with drill is exchanged for bit holders and bits within a matter of seconds, without any tools.

Choose between a **complete set** of 2 battery packs, charger and a robust plastic case or the **machine without accessories** in a box if you already have some batteries. Of course, you can also purchase battery packs and chargers separately. By the way, all Metabo battery packs are covered by a **3-year warranty**, regardless of the number of charging cycles.

Additional details such as the bright **LED work light** and the practical **belt hook** provide even more comfort when working.

**Advantage:****Batteries are 100% compatible – now also across different manufacturers.**

All 18 V devices and battery packs from CAS partners are 100% compatible with each other. CAS stands for "Cordless Alliance System".

**Supplied with:**

With quick-clamping drill chuck, without battery, without charger.

**Note:**

See No. 073870 – 073890 for suitable batteries and chargers.

## Technical description

|  |   |
|--|---|
| suitable battery - supplier / battery type / voltage | Type CAS 18 V   |
| Battery voltage                                      | 18 V  |
| Quick-clamping chuck range                           | 1.5 - 13 mm   |
| Number of rechargeable batteries contained           | 0   |
| Motor design   | brushless   |
| maximum twist drill size Ø in steel                  | 13 mm   |
| Power supply   | Mains operated  |
| Weight without battery                               | 1.7 kg  |
| Manufacturer's designation                           | BS 18 LTX BL I  |
| maximum torque soft                                  | 65 Nm   |
| Type of rechargeable battery                         | Lithium-ion   |
| Packaging  | Metabox   |
| maximum twist drill size Ø in wood                   | 68 mm   |
| typical application                                  | Heavy Duty  |
| maximum torque hard                                  | 130 Nm  |
| No load speed  | 0 - 550 min <sup>-1</sup>   |
| No load speed  | 0 - 2000 min <sup>-1</sup>  |
| Type of product                                      | Drill/drivers   |
| USP1   | 18V   |
| USP2   | Brushless motor, without rechargeable battery, quick-change chuck clamping range 1.5-13 |