

**GWX angle grinder without battery, Type: GWX1810SC****Order data**

Order number	077011 GWX1810SC
GTIN	3165140962452
Item class	03C

Description**Version:**

- **Easy and quick:** Easy change of angle grinder accessories without any parts that could be lost or need for additional tools.
- **Additional wrench no longer required.**
- **Comprehensive:** Huge range of angle grinders and accessories with complete backwards compatibility.
- **Maximum convenience** thanks to completely tool-less and quick accessory replacement.
- **Reliable:** Directional accessories can no longer be mounted incorrectly thanks to the innovative X-LOCK system. Maximum user protection thanks to acoustic signal upon correct mounting.
- **Clean working without annoying scratches! Less prominent and fewer scuffs with X-Lock angle grinders.**

The angle grinder has a Bluetooth connectivity module and user interface, as well as Drop Control, X-Brake and restart protection. It is possible to change accessories quickly and conveniently thanks to the keyless X-LOCK click system.

Supplied with:

Supplied with additional vibration control handle, safety guard, L-BOXX 136.

Note:

Suitable ProCore 18-V batteries and starter sets can be found under No. 073857 size C18 and No. 073865 size C18

Technical description

Data sheet

Power supply	Mains operated
Packaging	Modular case (L-Boxx)
Toolholder	X-LOCK system
Speed range	4500 - 9000 min ⁻¹
Interface	Bluetooth interface
Restart block	yes
Special features	Variable speed; restart protection; Drop Control
suitable battery - supplier / battery type / voltage	Bosch 18 V
Kick-back stop	yes
Battery voltage	18 V
Series	X-LOCK system
Weight	2 kg
Manufacturer's designation	GWX 18V-10 SC
maximum disc Ø	125 mm
Type of rechargeable battery	Lithium-ion
Number of rechargeable batteries contained	0
Type of product	Angle grinder

Accessories

Battery charger Type 1880CV	073866 1880CV
Battery charger Type GAL18160C	073866 GAL18160C
Battery charger Type GAL18V6-80	073866 GAL18V6-80
Battery starter setProCore Battery type, battery voltage C18 V	073865 C18
Li-ion batteryProCore Battery type, battery voltage C18 V	073857 C18