

**Garant**
**Fine boring head Ø 9.75 – 88.1 mm, Connection: HW63**


## Order data

Order number	237591 HW63
GTIN	4045197608444
Item class	29W

## Description

**Version:**

As Monoblock or with HW63 connection. With internal coolant supply Compact design.

**Application:**

For boring bars with shank Ø 16 mm and precision boring bridges. With ISO indexable inserts **type CC..0602...**

**Recommendation:**

Best with indexable inserts No. 237695 and No. 237696.

Through-coolant: yes

External Ø D<sub>1</sub>: 55 mm

Overhang A: 50 mm

## Technical description

External Ø D <sub>1</sub>	55 mm
Connection	HW63
Overhang A	50 mm
Through-coolant	yes
Type of product	Boring tool

