

**Garant****Adapter, Ø Dmin: 9,9mm****Order data**

Order number	237624 9,9
GTIN	4045197681522
Item class	29W

**Description****Application:**

For micro-boring heads No. 237495 and No. 237498.

With adaptor allows inserts No. 237625.

Boring range Ø 6.9 – 19.1 mm.

**Technical description**

Minimum Ø D <sub>min</sub>	9.9 mm
Type	D10
Boring range Ø	9.9 - 19.1 mm
Length L	61 mm
L <sub>2</sub>	35 mm
Shank Ø	7 mm
Through-coolant	yes
Type of product	Boring tool