

Garant**Insert, Ø Dmin: 6,9mm**

Order data

Order number	237625 6,9
GTIN	4045197681539
Item class	29W

Description

Application:

For micro-boring heads No. 237495 and No. 237498.

With adaptor allows inserts No. 237625.

Boring range Ø 6.9 – 19.1 mm.

Technical description

Minimum Ø D _{min}	6.9 mm
Boring range Ø	6.9 - 8.1 mm
for type	D07
maximum bore depth	30 mm
Type of product	Boring tool

