

Garant**Insert, Ø Dmin: 7,9mm**

Order data

Order number	237625 7,9
GTIN	4045197681546
Item class	29W

Description

Application:

For micro-boring heads No. 237495 and No. 237498.

With adaptor allows inserts No. 237625.

Boring range Ø 6.9 – 19.1 mm.

Technical description

Minimum Ø D _{min}	7.9 mm
for type	D07
maximum bore depth	30 mm
Boring range Ø	7.9 - 9.1 mm
Type of product	Boring tool

