


CNGA 120408, KBN25M, Type: MEW

Order data

Order number	255616 MEW
GTIN	4960664507139
Item class	25H

Description
Version:

MEGACOAT coated CBN inserts. MultiEdge Wiper; 2 cutting edges per insert with wiper geometry.

Grade: KBN25M

Cutting edge version: MEW

Cutting depth a_p : 0.05 - 0.2 mm

Feed f : 0.15 - 0.3 mm/rev.

Cutting speed v_c main application: 120 - 200 m/min

Technical description

Cutting depth a_p	0.05 - 0.2 mm
Cutting edge version	MEW
Cutting speed v_c main application	120 - 200 m/min
Feed f	0.15 - 0.3 mm/rev.
Corner radius	0.8 mm

Cutting conditions	heavily interrupted
Grade	KBN25M
Finishing/roughing assignment	Finishing
Tool material	CBN
ISO code indexable insert	CNGA 120408
Number of changes/inserts	2
Product name attribute	KBN25M
Type of product	Indexable insert for turning

User data

	Suitability	V _c	ISO code
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
continuous	suitable only under restricted conditions		
irregular	suitable		
interrupted	suitable only under restricted conditions		
dry	suitable		