

Garant
Fine boring head Ø 9.75 – 88.1 mm, Connection: HSK63

Order data

Order number	237591 HSK63
GTIN	4045197608475
Item class	29W

Description
Version:

As Monoblock or with HW63 connection. With internal coolant supply Compact design.

Application:

For boring bars with shank Ø 16 mm and precision boring bridges. With ISO indexable inserts type CC..0602...

Recommendation:

Best with indexable inserts No. 237695 and No. 237696.

Through-coolant: yes

External Ø D₁: 55 mm

Reach L₁: 72 mm

Overhang A: 95 mm

Technical description

Reach L ₁	72 mm
External Ø D ₁	55 mm
Connection	HSK63
Overhang A	95 mm
Through-coolant	yes
Type of product	Boring tool

