

Garant**Insert, Ø Dmin: 9,9mm**

Order data

Order number	237625 9,9
GTIN	4045197681560
Item class	29W

Description

Application:

For micro-boring heads No. 237495 and No. 237498.

With adaptor allows inserts No. 237625.

Boring range Ø 6.9 – 19.1 mm.

Technical description

for type	D10
Boring range Ø	9.9 - 12.1 mm
maximum bore depth	35 mm
Minimum Ø D _{min}	9.9 mm
Type of product	Boring tool

