

Garant**Insert, Ø Dmin: 11,9mm**

Order data

Order number	237625 11,9
GTIN	4045197681577
Item class	29W

Description

Application:

For micro-boring heads No. 237495 and No. 237498.

With adaptor allows inserts No. 237625.

Boring range Ø 6.9 – 19.1 mm.

Technical description

Minimum Ø D _{min}	11.9 mm
maximum bore depth	35 mm
Boring range Ø	11.9 - 14.1 mm
for type	D10
Type of product	Boring tool

