

Garant**Insert, Ø Dmin: 13,9mm**

Order data

Order number	237625 13,9
GTIN	4045197681584
Item class	29W

Description

Application:

For micro-boring heads No. 237495 and No. 237498.

With adaptor allows inserts No. 237625.

Boring range Ø 6.9 – 19.1 mm.

Technical description

maximum bore depth	35 mm
Minimum Ø D _{min}	13.9 mm
for type	D10
Boring range Ø	13.9 - 19.1 mm
Type of product	Boring tool

