

**Garant**
**Precision boring set  $\varnothing$  9.75 – 88.1 mm, Connection: SK40**

**Order data**

Order number	237586 SK40
GTIN	4045197608413
Item class	29W

**Description**
**Version:**

With fine boring head No. 237591, boring bars and accessories in a case. **Adjustment accuracy 0.01 mm per graduation / with vernier 0.002 mm on the  $\varnothing$ .**

$\varnothing$  adjustment with minimum backlash.

**For  $\varnothing$  9.75 – 88.1 mm**

**Application:**

For boring bars with shank  $\varnothing$  16 mm and precision boring bridges. With ISO indexable inserts **type CC..0602...**

**Supplied with:**

1 spindle nose: No. 237591 SK40

1 each boring bar (max. boring length): No. 237630  $\varnothing$  9.75 – 15.1 mm (30 mm), No. 237632  $\varnothing$  14.75 - 20.1 mm (51 mm);

No. 237634  $\varnothing$  19.75 – 25.1 mm (72 mm), No. 237636  $\varnothing$  24.75 - 30.1 mm (82 mm).

1 each boring bar (max. boring length): No. 237640  $\varnothing$  29.75 – 48.1 mm (85 mm), No. 237642  $\varnothing$  47.75 – 88.1 mm (85 mm).

1 insert toolholder for the bridge: No. 237564 06

1 insert: No. 260052 size CU7010 (CCMT 060204)

**Spare part:**

Insert screw No. 219830.

**Recommendation:**

Best with indexable inserts No. 237695 and No. 237696.

**Technical description**

Connection	SK40
Through-coolant	yes
Type of product	Boring tool

**Accessories**

Boring bar	237632
Adjustable boring bar	237640
Boring bar	237634
Boring bar	237636
Adjustable boring bar	237642
Fine boring head $\varnothing$ 9.75 – 88.1 mm Connection SK40	237591 SK40
CC.T 060204 Grade CU7010	260052 CU7010
Boring bar	237630
Set without arbor $\varnothing$ 9.75 – 88.1 mm	237599