

Garant**Screw-on toolholder, right-hand, Shank / insert size: 25/10mm****Order data**

Order number	260606 25/10
GTIN	4045197655370
Item class	21T

Technical description

Insert size	10 mm
Shank size	25 mm
suitable indexable insert	RC.T 1003
Shim screw	269013 2
Pack of insert screws	269028 2
Functional width L ₄	32 mm
ISO code toolholder	SRGCR/L 2525M10
Head length L ₁	21 mm
Shim	269005 11
Overall length L	150 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	30 degrees
Application	External longitudinal turning
Application	External longitudinal turning

Type of product	Boring bar
-----------------	------------

Accessories

Shim screw Type 2	269013 2
Set of insert screws Type 2	269028 2
Shim Type 11	269005 11
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500