



Pipe cutter stainless steel (VA) / copper, for pipe outer Ø up to: 42mm



Order data

Order number	819451 42
GTIN	4039976020855
Item class	86A

Description

Version:

Robust design for high loadings and sturdy spindle guidance; 2 or 4 guide rollers and precise cutter wheel / guide roller bearings ensure accurate operation and a square cut.

Application:

For cutting stainless steel and copper pipes up to max. 4 mm wall thickness.

Technical description

Cutter wheel Ø	20 mm
for pipe outer Ø	6 - 42 mm