

Wall/table-mounted eye-wash, Type: 714



Order data

Order number	984151 714
GTIN	4251138221270
Item class	97S

Description

Version:

Eye-washes for indoors with high-performance shower heads for a limited, uniform jet of water. With integrated automatic volume regulator to ensure the correct jet height regardless of the water pressure, as well as integrated backflow preventer to protect the drinking water network. Rubber sleeves around the shower head protect the person seeking help from injuries caused by impacts. Dust covers open automatically due to the water pressure when the eye-wash is operated. Large holes in the shower heads prevent stagnant water and thus limescale. with 2 shower heads, angled at 45°

Standard:

DIN EN 15154-2:2006, ANSI Z358.1-2015, DVGW NW-0417CL0263

Technical description

Flow pressure (bar)	2.5 - 5 bar
Flow pressure (bar)	36.26 - 72.52 lbf/in
Installation situation	wall-mounted
Installation situation	table-mounted

Flow rate	14 l/min
Depth	65 mm
Weight	0.95 kg
Height	310 mm
Function	Eye-wash
Function	Hand washing station
Width	145 mm
BSP connection thread	1/2 int. thread in
Type of product	Eye-wash