

## Wall/table-mounted eye-wash, Type: 712



### Order data

Order number	984151 712
GTIN	4251138221232
Item class	97S

### Description

#### Version:

Eye-washes for indoors with high-performance shower heads for a limited, uniform jet of water. With integrated automatic volume regulator to ensure the correct jet height regardless of the water pressure, as well as integrated backflow preventer to protect the drinking water network. Rubber sleeves around the shower head protect the person seeking help from injuries caused by impacts. Dust covers open automatically due to the water pressure when the eye-wash is operated. Large holes in the shower heads prevent stagnant water and thus limescale. with one shower head

#### Standard:

DIN EN 15154-2:2006, ANSI Z358.1-2015, DVGW NW-0417CL0263

### Technical description

Installation situation	wall-mounted
Installation situation	table-mounted
Flow pressure (bar)	2.5 - 5 bar
Flow rate	7 l/min

Flow pressure (bar)	36.26 - 72.52 lbf/in
Weight	0.8 kg
Hose length	1500 mm
Width	65 mm
Function	Eye-wash
Function	Hand washing station
Depth	65 mm
Height	240 mm
BSP connection thread	1/2 int. thread in
Type of product	Eye-wash