

**Cordless inspection camera, Manufacturer's designation: GIC12V****Order data**

|              |               |
|--------------|---------------|
| Order number | 492710 GIC12V |
| GTIN         | 4059952657240 |
| Item class   | 03B           |

**Description****Version:**

- 127 mm / 5 inch colour LCD display.
- Automatic rotation of the image ("Up is Up"<sup>™</sup> function).
- Transmission of images and videos directly via microUSB cable or microSD card.

Compact cordless inspection camera for visual inspection of places that are difficult to access.

**Function:**

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

**Supplied with:**

Supplied with 1 × 12 V / 2.0 Ah Li-ion battery, charger, 32 GB microSD card, camera cable No. 492716 size 1.5, micro-USB cable, hook, magnet, mirror, L-BOXX.

**Technical description**

|                    |               |
|--------------------|---------------|
| Weight             | 0.7 kg        |
| Display resolution | 1280 × 720 px |
| Camera head Ø      | 8.3 mm        |

|  |                        |
|--|------------------------|
| Display size   | 5 in                   |
| Battery voltage                                      | 12 V                   |
| Battery capacity                                     | 2 Ah                   |
| IP Index of Protection                               | IP 54                  |
| Length of the camera cable                           | 1500 mm                |
| suitable battery - supplier / battery type / voltage | Bosch 12 V             |
| Packaging  | Carrying case (L-Boxx) |
| Type of product                                      | Endoscope              |