

Emergency shower, Type: 837



Order data

Order number	984161 837
GTIN	4251138218218
Item class	97S

Description

Version:

Emergency body shower with eye-wash with collection basin, for floor mounting. Free-standing emergency showers are used when the shower cannot be mounted on the wall or a central location for first aid needs to be provided. With high-performance shower head for a limited, uniform and soft jet of water. Choice of flow rates from 50 to 110 litres per minute. Self-emptying, largely limescale-free and maintenance-free, and very robust and corrosion-resistant. Chemical-resistant polyester powder coating for use in aggressive environments.

Standard:

DIN EN 15154-1:2006, DIN EN 15154-2:2006, DIN EN 15154-5:2019, ANSI Z358.1-2014, DVGW NW-0416CL0425, DVGW NW-0417CL0263

Technical description

Flow pressure (bar)	1.5 - 3 bar
Flow pressure (bar)	2.5 - 5 bar
Emergency shower flow rate	50 l/min
BSP connection thread	1.1/4 in

Application range	Internal
Eye/face washing station flow rate	14 l/min
Depth	630 mm
Flow pressure (bar)	21.76 - 43.51 lbf/in
Flow pressure (bar)	36.26 - 72.52 lbf/in
Height	2330 mm
Installation situation	floor-mounted
Width	425 mm
Weight	15.4 kg
Type of product	Emergency shower