



Stainless steel inner / outer deburrer, Type: 10-54E



Order data

Order number	814921 10-54E
GTIN	4039976085830
Item class	86A

Description

Version:

Body of anodised aluminium, deburring cone of hardened special steel. Including external hexagon drive at each end – permits power deburring (up to 300 rpm).

Application:

Professional internal and external deburring of stainless steel, steel, copper, plastic and aluminium pipes. **Ideal for stainless steel pipes.**

Technical description

machine deburring available	yes
for pipe Ø	10 - 54 mm
Material of body	anodised aluminium
Type of product	Deburrers