



One-hand pipe bender set in a sheet steel case, Type: 1



Order data

Order number	821201 1
GTIN	4039976026369
Item class	84C

Description

Version:

Robust bending drive of cast aluminium with mechanical rack advance (quick advance and quick withdraw), a universal slide carrier, and bending formers of glass fibre-reinforced polyamide. Bending angles of up to 180° achievable.

Application:

For bending soft copper pipes, including sheathed ones, sheathed steel pipes of the mapress C-Stahl push-fitting system, soft precision steel pipes to DIN 2391 – 2394, plain or sheathed and connecting pipes of the push-fitting systems.

Content:

Bending drive: 1 pc.

Universal slide: 1 pc.

1 each bending segment for pipe external Ø: Size 12; 15; 18; 22 mm

Bending radius (centre of pipe): Size 36; 55; 72; 86 mm

Technical description

maximum bending angle	180 degrees
Type of product	Bending machine

