



Cordless drill / driver 18 V, 2-speed, quick-release chuck clamping range 1,5-13, in carrying case, Type: 7113246H1



Order data

Order number	070205 7113246H1
GTIN	
Item class	03F

Description

Version:

2 and 4 speed cordless drill/driver

- For precise drilling and screwdriving results.
- Electronic speed control for smooth, safe starts to drilling and screw driving; reversible.
- Sturdy metal gearbox for long working life.
- Good weight balance and ergonomics with softgrip inserts for non-tiring continuous work.
- Maximum work progress with AMPShare 18V ProCore rechargeable batteries: COOLPACK 2.0 technology provides 135% longer battery life. State-of-the-art cell technology and intelligent battery management provide 87% more power than conventional batteries.

2-speed cordless drill/driver with brushless motor and QuickIN interface. Perfectly suited to drilling and tapping up to 10 mm.

- **Mechanical torque setting.**
- **Compact design.**
- **Brushless FEIN PowerDrive motor with 30% higher efficiency and long working life.**

Supplied with:

Supplied with battery and charger. QuickIN drill chuck, belt clip, bit holder, L-BOXX

Technical description

Quick-clamping chuck range	1.5 - 13 mm
----------------------------	-------------

maximum torque soft	38 Nm
Weight	1.7 kg
maximum twist drill size Ø in steel	13 mm
Type of rechargeable battery	Lithium-ion
maximum speed 2nd speed	2000 min ⁻¹
maximum speed 1st speed	450 min ⁻¹
maximum twist drill size Ø in wood	50 mm
Manufacturer's designation	ABS 18 Q AS
Packaging	Modular case (L-Boxx)
typical application	Strong
maximum torque hard	60 Nm
Power supply	Mains operated
maximum vibration to EN	<2,5 m/s ²
Battery voltage	18 V
Battery capacity	4 Ah
suitable battery - supplier / battery type / voltage	Bosch 18 V
Type of product	Drill/driver
USP1	18V, 2-speed
USP2	Quick-release chuck clamping range 1.5-13, in a carrying case

Accessories

Li-ion battery Battery type, battery voltage B18 V	073851 B18
Li-ion battery Battery type, battery voltage B18 V	073853 B18
Li-ion battery Battery type, battery voltage B18 V	073854 B18
Li-ion batteryProCore Battery type, battery voltage C18 V	073856 C18
Li-ion batteryProCore Battery type, battery voltage C18 V	073857 C18
Li-ion batteryProCore Battery type, battery voltage C18 V	073858 C18

Li-ion batteryProCore+ Battery capacity 8 A·h	073860 8
Battery starter setProCore+ Battery capacity 8 A·h	073861 8
Battery starter setProCore Battery type, battery voltage C18 V	073863 C18
Battery starter setProCore Battery type, battery voltage C18 V	073865 C18
Battery starter setProCore Battery type, battery voltage C18 V	073867 C18