



Cordless drill/driver, Type: 71132461



Order data

Order number	070200 71132461
GTIN	4014586898872
Item class	03F

Description

Version:

2 and 4 speed cordless drill/driver

- For precise drilling and screwdriving results.
- Electronic speed control for smooth, safe starts to drilling and screw driving; reversible.
- Sturdy metal gearbox for long working life.
- Good weight balance and ergonomics with softgrip inserts for non-tiring continuous work.
- Maximum work progress with AMPShare 18V ProCore rechargeable batteries: COOLPACK 2.0 technology provides 135% longer battery life. State-of-the-art cell technology and intelligent battery management provide 87% more power than conventional batteries.

2-speed cordless drill/driver with brushless motor and QuickIN interface. Perfectly suited to drilling and tapping up to 10 mm.

- Mechanical torque setting.
- Compact design.
- Brushless FEIN PowerDrive motor with 30% higher efficiency and long working life.

Supplied with:

QuickIN drill chuck, belt clip, bit holder, L-BOXX

Attention:

German version. Order free UK adapter plug No. 08 1172_GB.

Note:

See No. 073851 – 073866 for suitable batteries, chargers and starter sets.

Technical description

maximum twist drill size Ø in wood	50 mm
maximum speed 2nd speed	2000 min ⁻¹
maximum torque hard	60 Nm
typical application	Strong
Manufacturer's designation	ABS 18 Q AS Select
suitable battery - supplier / battery type / voltage	Bosch 18 V
maximum twist drill size Ø in steel	13 mm
maximum torque soft	38 Nm
Type of rechargeable battery	Lithium-ion
Power supply	Mains operated
maximum vibration to EN	<2,5 m/s ²
Battery voltage	18 V
Quick-clamping chuck range	1.5 - 13 mm
Weight	1.4 kg
Packaging	Modular case (L-Boxx)
maximum speed 1st speed	450 min ⁻¹
Type of product	Drill/driver
USP1	4-speed gearbox. 18V
USP2	Suitable for wood & steel, quick-release chuck clamping range 1.5-13, without rechargeable battery

Accessories

Battery starter set Type 92604324	073832 92604324
-----------------------------------	-----------------

Li-ion battery Rechargeable battery type, battery voltage
FE18 V

073837 FE18