



Cordless drill/driver without rechargeable battery and charger, Type: 71161561



Order data

Order number	070200 71161561
GTIN	4014586900100
Item class	03F

Description

Version:

2 and 4 speed cordless drill/driver

- For precise drilling and screwdriving results.
- Electronic speed control for smooth, safe starts to drilling and screw driving; reversible.
- Sturdy metal gearbox for long working life.
- Good weight balance and ergonomics with softgrip inserts for non-tiring continuous work.
- Maximum work progress with AMPShare 18V ProCore rechargeable batteries: COOLPACK 2.0 technology provides 135% longer battery life. State-of-the-art cell technology and intelligent battery management provide 87% more power than conventional batteries.

4-speed cordless drill/driver with brushless motor and QuickIN MAX interface. No

compromise on performance when drilling and tapping up to 13 mm.

- 4-speed all-metal gearbox. With rotational speeds of up to 4000 rpm for optimum cutting speeds in metal when working on any bore from 1.5 to 80 mm.
- The powerful brushless FEIN PowerDrive motor, with up to 30% higher efficiency, enables a longer service life.

- **Safe and controlled working thanks to kickback control, restart protection, overload protection and extendable additional handle.**
- **The innovative reset function enables screwdriving work in wood at a reduced speed for perfect results.**
- **Intuitive control panel with dimmable LED to perfectly illuminate the work area depending on the material.**

Supplied with:

Without battery and charger. QuickIN drill chuck, belt clip, handle, bit holder, L-BOXX

Attention:

German version. Order free UK adapter plug No. 08 1172_GB.

Note:

See No. 073851 – 073866 for suitable batteries, chargers and starter sets.

Technical description

suitable battery - supplier / battery type / voltage	Bosch 18 V
typical application	Heavy Duty
maximum speed 2nd speed	850 min ⁻¹
maximum twist drill size Ø in wood	60 mm
Manufacturer's designation	ASCM 18-4 QM AS Select
Type of rechargeable battery	Lithium-ion
maximum twist drill size Ø in steel	13 mm
Packaging	Modular case (L-Boxx)
Power supply	Mains operated
maximum vibration to EN	<2,5 m/s ²
maximum torque hard	90 Nm
maximum speed 4th speed	4000 min ⁻¹
Battery voltage	18 V
maximum torque soft	45 Nm
maximum speed 1st speed	430 min ⁻¹
Quick-clamping chuck range	1.5 - 13 mm
Weight	1.3 kg
maximum speed 3rd speed	2000 min ⁻¹
Type of product	Drill/driver

USP1	4-speed gearbox. 18V
USP2	Suitable for wood & steel, quick-release chuck clamping range 1.5-13, without rechargeable battery

Accessories

Battery starter set Type 92604324	073832 92604324
Li-ion battery Rechargeable battery type, battery voltage FE18 V	073837 FE18