



Cordless drill / driver 18 V, 2-speed, quick-release chuck clamping range 1,5-13, in carrying case, Type: 71161561H1



Order data

Order number	070205 71161561H1
GTIN	
Item class	03F

Description

Version:

2 and 4 speed cordless drill/driver

- For precise drilling and screwdriving results.
- Electronic speed control for smooth, safe starts to drilling and screw driving; reversible.
- Sturdy metal gearbox for long working life.
- Good weight balance and ergonomics with softgrip inserts for non-tiring continuous work.
- Maximum work progress with AMPShare 18V ProCore rechargeable batteries: COOLPACK 2.0 technology provides 135% longer battery life. State-of-the-art cell technology and intelligent battery management provide 87% more power than conventional batteries.

4-speed cordless drill/driver with brushless motor and QuickIN MAX interface. No

compromise on performance when drilling and tapping up to 13 mm.

- 4-speed all-metal gearbox. With rotational speeds of up to 4000 rpm for optimum cutting speeds in metal when working on any bore from 1.5 to 80 mm.
- The powerful brushless FEIN PowerDrive motor, with up to 30% higher efficiency, enables a longer service life.
- Safe and controlled working thanks to kickback control, restart protection, overload protection and extendable additional handle.

- **The innovative reset function enables screwdriving work in wood at a reduced speed for perfect results.**
- **Intuitive control panel with dimmable LED to perfectly illuminate the work area depending on the material.**

Supplied with:

Supplied with battery and charger. QuickIN drill chuck, belt clip, handle, bit holder, L-BOXX

Technical description

Manufacturer's designation	ASCM 18-4 QM AS
maximum speed 3rd speed	2000 min ⁻¹
maximum speed 1st speed	430 min ⁻¹
Weight	1.8 kg
Battery capacity	4 Ah
Packaging	Modular case (L-Boxx)
suitable battery - supplier / battery type / voltage	Bosch 18 V
Type of rechargeable battery	Lithium-ion
maximum torque soft	45 Nm
typical application	Heavy Duty
Quick-clamping chuck range	1.5 - 13 mm
maximum twist drill size Ø in wood	60 mm
maximum twist drill size Ø in steel	13 mm
maximum speed 2nd speed	850 min ⁻¹
maximum vibration to EN	<2,5 m/s ²
Power supply	Mains operated
maximum speed 4th speed	4000 min ⁻¹
Battery voltage	18 V
maximum torque hard	90 Nm
Type of product	Drill/driver
USP1	18V, 2-speed
USP2	Quick-release chuck clamping range 1.5-13, in a carrying case

Accessories

Li-ion battery Battery type, battery voltage B18 V	073851 B18
Li-ion battery Battery type, battery voltage B18 V	073853 B18
Li-ion battery Battery type, battery voltage B18 V	073854 B18
Li-ion batteryProCore Battery type, battery voltage C18 V	073856 C18
Li-ion batteryProCore Battery type, battery voltage C18 V	073857 C18
Li-ion batteryProCore Battery type, battery voltage C18 V	073858 C18
Li-ion batteryProCore+ Battery capacity 8 A·h	073860 8
Battery starter setProCore+ Battery capacity 8 A·h	073861 8
Battery starter setProCore Battery type, battery voltage C18 V	073863 C18
Battery starter setProCore Battery type, battery voltage C18 V	073865 C18
Battery starter setProCore Battery type, battery voltage C18 V	073867 C18