



Drill/driver 18 V, cordless drill/driver, suitable for wood & steel, quick-action chuck clamping range 1.5-13



Order data

Order number	070200 71161461
GTIN	4014586898919
Item class	03F

Description

Version:

Cordless drill/driver

- For precise drilling and screwdriving results.
- Electronic speed control for smooth, safe starts to drilling and screw driving; reversible.
- Sturdy metal gearbox for long working life.
- Good weight balance and ergonomics with softgrip inserts for non-tiring continuous work.
- Maximum work progress with AMPShare 18V ProCore rechargeable batteries: COOLPACK 2.0 technology provides 135% longer battery life. State-of-the-art cell technology and intelligent battery management provide 87% more power than conventional batteries.

Small and light 4-speed cordless drill/driver with brushless motor and QuickIN interface. Perfectly suited to universal drilling and screwdriving work up to 8 mm.

- Solid metal 4-speed gearbox for optimum cutting speeds for drilling in metal and self-tapping screwdriving work up to 6 mm.
- Brushless FEIN PowerDrive motor with 30% higher efficiency and long working life.
- Mechanical torque setting.

- **Extensive user protection features include restart protection, electronic overload protection and brake.**

Supplied with:

Without battery and charger. QuickIN drill chuck, belt clip, bit holder, L-BOXX

Attention:

German version. Order free UK adapter plug No. 08 1172_GB.

Note:

See No. 073851 - 073866 for suitable rechargeable batteries and chargers.

Technical description

maximum speed 3rd speed	1400 min ⁻¹
Weight	1.3 kg
Manufacturer's designation	ASCM 18 QSW AS Select
suitable battery - supplier / battery type / voltage	Bosch 18 V
maximum speed 1st speed	400 min ⁻¹
Packaging	Modular case (L-Boxx)
maximum torque hard	40 Nm
maximum torque soft	30 Nm
maximum twist drill size Ø in steel	13 mm
maximum vibration to EN	<2.5 m/s ²
Battery voltage	18 V
Type of rechargeable battery	Lithium-ion
maximum twist drill size Ø in wood	40 mm
maximum speed 4th speed	2500 min ⁻¹
typical application	Medium
Power supply	Mains operated
maximum speed 2nd speed	700 min ⁻¹
Quick-clamping chuck range	1.5 - 13 mm
Type of product	Drill/driver
USP1	18 V
USP2	Suitable for wood & steel, quick-release chuck clamping range 1.5-13

