



Cordless impact wrench / driver, Type: 71151261



Order data

Order number	074000 71151261
GTIN	4014586898902
Item class	03F

Description

Version:

Powerful cordless impact wrench with **brushless motor and torque adjustment in 6 steps**. Robust all-metal impact drive and ergonomic handling thanks to soft-grip coating.

- **Brushless FEIN PowerDrive motor with 30% higher efficiency and long working life.**
- **Impact nut is securely connected to the drive output square with a positive connection and form fit.**

Supplied with:

Version without battery and without charger, including L-BOXX. 1 pc. belt clip, 1 pc. bit holder.

Note:

See No. 073851 – 073866 for suitable batteries, chargers and starter sets.

Technical description

maximum vibration to EN	12.9 m/s ²
Packaging	Modular case (L-Boxx)
Tool arbor drive profile	External square drive

typical application	Heavy Duty
Number of rechargeable batteries contained	0
Type of rechargeable battery	Lithium-ion
Power supply	Mains operated
Battery voltage	18 V
Weight	3.1 kg
maximum screw \varnothing (8.8 - 12.9)	M27
suitable battery - supplier / battery type / voltage	Bosch 18 V
Manufacturer's designation	ASCD 18-1000 W34 AS
Tool arbor size	3/4 in
Number of impacts	0 - 2200 min ⁻¹
maximum torque	1050 Nm
Type of product	Impact wrench

Accessories

Li-ion battery Battery type, battery voltage B18 V	073851 B18
Battery charger Type 1880CV	073866 1880CV
Battery charger Type GAL18160C	073866 GAL18160C
Battery charger Type GAL18V6-80	073866 GAL18V6-80