

**Cordless impact wrench 12 V/18 V, suitable for heavy duty, Type: 71151161****Order data**

Order number	074000 71151161
GTIN	4014586898896
Item class	03F

Description**Version:**

Powerful cordless impact wrench with **brushless motor and torque adjustment in 6 steps**. Robust all-metal impact drive and ergonomic handling thanks to soft-grip coating.

- **Brushless motor with 30% higher efficiency and long working life.**
- **1/4 inch hexagon socket toolholder for holding bits and sockets.**
- **10% higher torque for anti-clockwise rotation to release stubborn stuck screws.**

Supplied with:

Version without battery and without charger, including L-BOXX. 1 pc. belt clip, 1 pc. bit holder.

Note:

See No. 073851 – 073866 for suitable batteries, chargers and starter sets.

Technical description

maximum torque	210 Nm
Packaging	Modular case (L-Boxx)
Type of rechargeable battery	Lithium-ion

Power supply	Mains operated
suitable battery - supplier / battery type / voltage	Bosch 18 V
Tool arbor size	1/4 in
Battery voltage	18 V
Tool arbor drive profile	HEX
Number of rechargeable batteries contained	0
Weight	1.2 kg
typical application	Heavy Duty
maximum screw Ø (8.8 - 12.9)	M18
maximum vibration to EN	6 m/s ²
Manufacturer's designation	ASCD 18-200 W4 AS
Number of impacts	0 - 3000 min ⁻¹
Type of product	Impact wrench