



Cordless impact wrench / driver, Type: 71151161



Order data

Order number	074000 71151161
GTIN	4014586898896
Item class	03F

Description

Version:

Powerful cordless impact wrench with **brushless motor and torque adjustment in 6 steps**. Robust all-metal impact drive and ergonomic handling thanks to soft-grip coating.

- **Brushless motor with 30% higher efficiency and long working life.**
- **1/4 inch hexagon socket toolholder for holding bits and sockets.**
- **10% higher torque for anti-clockwise rotation to release stubborn stuck screws.**

Supplied with:

Version without battery and without charger, including L-BOXX. 1 pc. belt clip, 1 pc. bit holder.

Note:

See No. 073851 – 073866 for suitable batteries, chargers and starter sets.

Technical description

maximum torque	210 Nm
Packaging	Modular case (L-Boxx)
Type of rechargeable battery	Lithium-ion

Power supply	Mains operated
suitable battery - supplier / battery type / voltage	Bosch 18 V
Tool arbor size	1/4 in
Battery voltage	18 V
Tool arbor drive profile	HEX
Number of rechargeable batteries contained	0
Weight	1.2 kg
typical application	Heavy Duty
maximum screw \varnothing (8.8 - 12.9)	M18
maximum vibration to EN	6 m/s ²
Manufacturer's designation	ASCD 18-200 W4 AS
Number of impacts	0 - 3000 min ⁻¹
Type of product	Impact wrench

Accessories

Li-ion battery Battery type, battery voltage B18 V	073851 B18
Battery charger Type 1880CV	073866 1880CV
Battery charger Type GAL18160C	073866 GAL18160C
Battery charger Type GAL18V6-80	073866 GAL18V6-80