

**Cordless impact wrench / driver, Type: 71151061****Order data**

Order number	074000 71151061
GTIN	4014586898889
Item class	03F

Description**Version:**

Powerful cordless impact wrench with **brushless motor and torque adjustment in 6 steps**. Robust all-metal impact drive and ergonomic handling thanks to soft-grip coating.

- **Brushless motor has 10% higher torque for anti-clockwise rotation to release stubborn stuck screws.**
- **Touch protection on the gear head.**
- **Compact design.**

Supplied with:

Version without battery and without charger, including L-BOXX. 1 pc. belt clip, 1 pc. bit holder.

Note:

See No. 073851 – 073866 for suitable batteries, chargers and starter sets.

Technical description

maximum vibration to EN	6 m/s ²
Manufacturer's designation	ASCD 18-300 W2 AS

Packaging	Modular case (L-Boxx)
Battery voltage	18 V
Power supply	Mains operated
Number of rechargeable batteries contained	0
maximum torque	290 Nm
maximum screw Ø (8.8 - 12.9)	M18
Tool arbor size	1/2 in
typical application	Heavy Duty
Weight	1.2 kg
Number of impacts	0 - 3400 min ⁻¹
Tool arbor drive profile	External square drive
suitable battery - supplier / battery type / voltage	Bosch 18 V
Type of rechargeable battery	Lithium-ion
Type of product	Impact wrench

Accessories

Battery charger Type 1880CV	073866 1880CV
Battery charger Type GAL18160C	073866 GAL18160C
Battery charger Type GAL18V6-80	073866 GAL18V6-80