

**Cordless drill / driver, Type: M18BLDDRC5****Order data**

Order number	070210 M18BLDDRC5
GTIN	4058546477066
Item class	03L

Description**Version:**

MILWAUKEE – Cordless power drill Powerful cordless 2-speed drill / driver, reversible. REDLITHIUM™ rechargeable batteries with **single-cell monitoring** and **charge status display**. Sturdy **metal gearbox** for long working life. **FIXTEC metal quick-clamping drill chuck** with spindle lock. LED illumination of the working area. Handle with Softgrip coating for comfortable use.

Supplied with:

Supplied with 2× M18 Red-Li-ion rechargeable batteries, M12-18 FC charger, belt clip, HD box (carrying case).

Note:

See No. 073816, No. 073827 and No. 073840 ff. for suitable replacement batteries and chargers.

Technical description

suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
Weight	1.8 kg
maximum speed 2nd speed	1700 min ⁻¹

Number of rechargeable batteries contained	2
Battery voltage	18 V
maximum vibration to EN	< 2,5 m/s ²
Quick-clamping chuck range	1.5 - 15 mm
maximum twist drill size Ø in steel	13 mm
maximum speed 1st speed	0 - 550 min ⁻¹
maximum twist drill size Ø in wood	52 mm
maximum torque hard	60 Nm
typical application	Strong
Motor design	Brushless motor
Manufacturer's designation	M18 BLDDRC-502C
Power supply	Mains operated
Battery capacity	5 Ah
Type of rechargeable battery	Lithium-ion
Packaging	Modular case (HD=Heavy Duty)
Type of product	Drill/driver